

Garant

Clamping toolholder PSSNL 45°, for indexable inserts SN., left-hand, Shank / insert size: 25/12mm



Order data

Order number	251113 25/12
GTIN	4045197650887
Item class	21T

Technical description

Lever screw	259018 2
Shim	259031 20
Lever	259015 2
Shim pins pack	259044 2
Shank size	25 mm
suitable indexable insert	SN.. 1204..
ISO code toolholder	PSSNR/L 2525M12
Insert size	12 mm
Shim punches pack	259047 2
Head length L ₁	29 mm
Functional width L ₄	32 mm
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 20	259031 20
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3