

Garant
**Clamping toolholder SDHCL 107,5°, for indexable inserts DC., left-hand,
Shank / insert size: 25/11 mm**

Order data

Order number	260307 25/11
GTIN	4045197655301
Item class	21T

Technical description

Pack of insert screws	269028 2
Head length L ₁	21 mm
ISO code toolholder	SDHCR/L 2525M11
Insert size	11 mm
Shim screw	269013 2
Shank size	25 mm
Functional width L ₄	32 mm
suitable indexable insert	DC.. 11T3..
Shim	269005 3
Overall length L	150 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15