

**Garant**
**Clamping toolholder SDHCR 107,5°, for indexable inserts DC., right-hand,  
Shank / insert size: 16/11 mm**

**Order data**

Order number	260306 16/11
GTIN	4045197652522
Item class	21T

**Technical description**

Insert size	11 mm
Pack of insert screws	269028 2
ISO code toolholder	SDHCR/L 1616H11
Shank size	16 mm
Head length L <sub>1</sub>	12 mm
Shim screw	269013 2
Functional width L <sub>4</sub>	20 mm
suitable indexable insert	DC.. 11T3..
Shim	269005 3
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15