

**Garant**

**Clamping toolholder SDJCL 93°, for indexable inserts DC., left-hand, Shank / insert size: 20/11mm**



## Order data

Order number	260309 20/11
GTIN	4045197652638
Item class	21T

## Technical description

Insert size	11 mm
Head length L <sub>1</sub>	20.5 mm
Shank size	20 mm
Functional width L <sub>4</sub>	25 mm
Pack of insert screws	269028 2
Shim screw	269013 2
Shim	269005 3
suitable indexable insert	DC.. 11T3..
ISO code toolholder	SDJCR/L 2020K11
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15