

**Garant**

**Clamping toolholder PSKNL 75°, for indexable inserts SN., left-hand, Shank / insert size: 32/19mm**



## Order data

Order number	251111 32/19
GTIN	4045197650849
Item class	21T

## Technical description

Lever screw	259018 13
Head length L <sub>1</sub>	34 mm
Shank size	32 mm
Shim pins pack	259044 7
ISO code toolholder	PSKNR/L 3232P19
Insert size	19 mm
Shim punches pack	259047 5
suitable indexable insert	SN.. 1906..
Lever	259015 13
Shim	259031 38
Functional width L <sub>4</sub>	40 mm
Overall length L	170 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 13	259015 13
Lever screw Type 13	259018 13
Shim Type 38	259031 38
Set of shim pins 10 pieces Type 7	259044 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 4 mm	674242 4