

**Garant**
**Clamping toolholder SDHCR 107,5°, for indexable inserts DC., right-hand,  
Shank / insert size: 20/11 mm**

**Order data**

Order number	260306 20/11
GTIN	4045197652539
Item class	21T

**Technical description**

Pack of insert screws	269028 2
Functional width $L_4$	25 mm
suitable indexable insert	DC.. 11T3..
Shim	269005 3
Shank size	20 mm
Head length $L_1$	15 mm
Insert size	11 mm
Shim screw	269013 2
ISO code toolholder	SDHCR/L 2020K11
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	107.5 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15