

Garant

Clamping toolholder SDJCL 93°, for indexable inserts DC., left-hand, Shank / insert size: 25/11mm



Order data

Order number	260309 25/11
GTIN	4045197652645
Item class	21T

Technical description

Head length L ₁	21.5 mm
Insert size	11 mm
ISO code toolholder	SDJCR/L 2525M11
Functional width L ₄	32 mm
Shim	269005 3
Pack of insert screws	269028 2
suitable indexable insert	DC.. 11T3..
Shim screw	269013 2
Shank size	25 mm
Overall length L	150 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15