

Garant
**Clamping toolholder SDJCR 93°, for indexable inserts DC., right-hand,
Shank / insert size: 16/11 mm**

Order data

Order number	260308 16/11
GTIN	4045197652584
Item class	21T

Technical description

suitable indexable insert	DC.. 11T3..
Functional width L ₄	20 mm
ISO code toolholder	SDJCR/L 1616H11
Shim screw	269013 2
Shank size	16 mm
Shim	269005 3
Insert size	11 mm
Head length L ₁	20 mm
Pack of insert screws	269028 2
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Shim Type 3	269005 3
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15