

Garant

**HSS boring bar AH.. SDUCL 93°, for indexable inserts DC., left-hand, Shank
Ø / insert size: 10/07mm**



Order data

Order number	260333 10/07
GTIN	4045197652980
Item class	21T

Technical description

ISO code toolholder	AH10K SDUCR/L07
suitable indexable insert	DC.. 0702..
Centre offset L ₃	9 mm
Insert size	7 mm
Overhang L ₁	50 mm
Pack of insert screws	269028 7
Minimum pre-drill Ø D _{min}	14 mm
Overall length L	125 mm
Clamping height L ₂	9 mm
Setting angle κ	93 degrees
Shank Ø D _s	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8