

Garant

**HSS boring bar AH.. SDQCR 107,5°, for indexable inserts DC., right-hand,
Shank Ø / insert size: 12/07mm**



Order data

Order number	260328 12/07
GTIN	4045197652805
Item class	21T

Technical description

Head length L_1	20 mm
ISO code toolholder	AH12M SDQCR/L07
Insert size	7 mm
Centre offset L_3	9.5 mm
Minimum pre-drill $\varnothing D_{min}$	16 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Overall length L	150 mm
Clamping height L_2	11 mm
Setting angle κ	107.5 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8