

**Garant**

**HSS boring bar AH.. SDQCR 107,5°, for indexable inserts DC., right-hand,  
Shank Ø / insert size: 16/07mm**


**Order data**

Order number	260328 16/07
GTIN	4045197652812
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Head length $L_1$	30 mm
ISO code toolholder	AH16Q SDQCR/L07
Minimum pre-drill $\varnothing D_{min}$	20 mm
Centre offset $L_3$	12 mm
Insert size	7 mm
Overall length $L$	180 mm
Clamping height $L_2$	15 mm
Setting angle $\kappa$	107.5 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8