

Garant

**HSS boring bar AH.. SDUCL 93°, for indexable inserts DC., left-hand, Shank
Ø / insert size: 1012/07mm**



Order data

Order number	260333 1012/07
GTIN	4045197652997
Item class	21T

Technical description

Insert size	7 mm
Pack of insert screws	269028 7
Centre offset L ₃	9 mm
ISO code toolholder	AH1012K SDUCR/L07
suitable indexable insert	DC.. 0702..
Neck width L ₄	10 mm
Head length L ₁	28 mm
Minimum pre-drill Ø D _{min}	15.5 mm
Overall length L	125 mm
Clamping height L ₂	11 mm
Setting angle κ	93 degrees
Usable depth T	5 mm
Shank Ø D _s	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D

Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8