

**Garant**

**HSS boring bar AH.. SDQCR 107,5°, for indexable inserts DC., right-hand,  
Shank Ø / insert size: 20/11mm**


**Order data**

Order number	260328 20/11
GTIN	4045197652829
Item class	21T

**Technical description**

ISO code toolholder	AH20R SDQCR/L11
Centre offset $L_3$	14.5 mm
Head length $L_1$	40 mm
Pack of insert screws	269028 8
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Overall length L	200 mm
Clamping height $L_2$	18 mm
Setting angle $\kappa$	107.5 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15