

Garant

HSS boring bar AH.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 1012/07mm



Order data

Order number	260332 1012/07
GTIN	4045197652911
Item class	21T

Technical description

Neck width L_4	10 mm
Head length L_1	28 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Centre offset L_3	9 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	AH1012K SDUCR/L07
Insert size	7 mm
Overall length L	125 mm
Clamping height L_2	11 mm
Setting angle κ	93 degrees
Usable depth T	5 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD

Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8