

**Garant**

**HSS boring bar AH.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 10/07mm**


**Order data**

Order number	260329 10/07
GTIN	4045197652843
Item class	21T

**Technical description**

Centre offset $L_3$	8 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	AH10K SDQCR/L07
Pack of insert screws	269028 7
Insert size	7 mm
Head length $L_1$	20 mm
Overall length $L$	125 mm
Clamping height $L_2$	9 mm
Setting angle $\kappa$	107.5 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8