

**Garant**

**HSS boring bar AH.. SDUCL 93°, for indexable inserts DC., left-hand, Shank  
Ø / insert size: 16/07mm**


**Order data**

Order number	260333 16/07
GTIN	4045197653024
Item class	21T

**Technical description**

Overhang $L_1$	80 mm
ISO code toolholder	AH16Q SDUCR/L07
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Pack of insert screws	269028 7
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Centre offset $L_3$	10 mm
Overall length L	180 mm
Clamping height $L_2$	15 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8