

**Garant**
**HSS boring bar AH.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 1216/07mm**

**Order data**

Order number	260332 1216/07
GTIN	4045197652935
Item class	21T

**Technical description**

suitable indexable insert	DC.. 0702..
Centre offset L <sub>3</sub>	11 mm
ISO code toolholder	AH1216M SDUCR/L07
Pack of insert screws	269028 7
Minimum pre-drill Ø D <sub>min</sub>	19.5 mm
Neck width L <sub>4</sub>	12 mm
Head length L <sub>1</sub>	36 mm
Insert size	7 mm
Overall length L	150 mm
Clamping height L <sub>2</sub>	15 mm
Setting angle κ	93 degrees
Usable depth T	5 mm
Shank Ø D <sub>s</sub>	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D

Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8