

**Garant**

**Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 10/07mm**


**Order data**

Order number	260342 10/07
GTIN	4045197656032
Item class	21T

**Technical description**

Centre offset $L_3$	7 mm
Pack of insert screws	269028 7
Head length $L_1$	40 mm
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	13.5 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	A10K SDUCR/L07
Overall length L	125 mm
Clamping height $L_2$	9 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8