

Garant**HSS boring bar AH.. SDQCL 107,5°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 16/07mm**

Order data

Order number	260329 16/07
GTIN	4045197652867
Item class	21T

Technical description

Minimum pre-drill Ø D _{min}	20 mm
Head length L ₁	30 mm
ISO code toolholder	AH16Q SDQCR/L07
Centre offset L ₃	12 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Overall length L	180 mm
Clamping height L ₂	15 mm
Setting angle κ	107.5 degrees
Shank Ø D _s	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8