

Garant
Carbide boring bar E.. SDUCR, for indexable inserts DC.., right-hand

Order data

Order number	260324
GTIN	4045197652751
Item class	29W

Technical description

suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
ISO code toolholder	E10K SDUCR/L07
ISO code toolholder	E12M SDUCR/L07
Clamping height L_2	9.6 mm
Clamping height L_2	11.6 mm
Centre offset L_3	7 mm
Centre offset L_3	9 mm
Minimum pre-drill $\varnothing D_{min}$	12 mm
Minimum pre-drill $\varnothing D_{min}$	15 mm
Overall length L	125 mm
Overall length L	150 mm
Standard	DIN 8024
Standard	Works standard

Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes
Type of product	Boring bar

Accessories

Boring bar carbide Shank Ø / insert size 10/07 mm	260318 10/07
Boring bar carbide Shank Ø / insert size 12/07 mm	260318 12/07
Set of insert screws Type 7	269028 7