

Garant

HSS boring bar AH.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 16/07mm

**Order data**

Order number	260332 16/07
GTIN	4045197652942
Item class	21T

Technical description

Overhang L_1	80 mm
suitable indexable insert	DC.. 0702..
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Centre offset L_3	10 mm
ISO code toolholder	AH16Q SDUCR/L07
Pack of insert screws	269028 7
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8