

Garant

Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 12/07mm


Order data

Order number	260342 12/07
GTIN	4045197653079
Item class	21T

Technical description

Pack of insert screws	269028 7
ISO code toolholder	A12L SDUCR/L07
Minimum pre-drill Ø D _{min}	16 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Centre offset L ₃	9 mm
Overall length L	140 mm
Clamping height L ₂	11 mm
Setting angle κ	93 degrees
Shank Ø D _s	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8