

Garant
HSS boring bar AH.. SDUCR, for indexable inserts DC.., right-hand

Order data

Order number	260334
GTIN	4045197653055
Item class	29W

Technical description

ISO code toolholder	AH0810H SDUCR/L07
ISO code toolholder	AH1216M SDUCR/L07
ISO code toolholder	AH1012K SDUCR/L07
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Clamping height L ₂	9 mm
Clamping height L ₂	11 mm
Clamping height L ₂	15 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Centre offset L ₃	7 mm
Centre offset L ₃	9 mm
Centre offset L ₃	11 mm

Head length L ₁	22 mm
Head length L ₁	28 mm
Head length L ₁	36 mm
Overall length L	100 mm
Overall length L	125 mm
Overall length L	150 mm
Neck width L ₄	8 mm
Neck width L ₄	10 mm
Neck width L ₄	12 mm
Usable depth T	5 mm
Usable depth T	5 mm
Usable depth T	5 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Type of product	Boring bar

Accessories

Boring bar HSS Shank Ø / insert size 0810/07 mm	260332 0810/07
Boring bar HSS Shank Ø / insert size 1012/07 mm	260332 1012/07
Boring bar HSS Shank Ø / insert size 1216/07 mm	260332 1216/07
Boring bar HSS Shank Ø / insert size 8/07 mm	260332 8/07
Set of insert screws Type 7	269028 7