

Garant

HSS boring bar AH.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	260332 20/11
GTIN	4045197652959
Item class	21T

Technical description

suitable indexable insert	DC.. 11T3..
Overhang L_1	100 mm
Centre offset L_3	16 mm
Insert size	11 mm
Pack of insert screws	269028 8
Minimum pre-drill $\varnothing D_{\min}$	26 mm
ISO code toolholder	AH20R SDUCR/L11
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15