

Garant

Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	260342 16/07
GTIN	4045197653086
Item class	21T

Technical description

ISO code toolholder	A16Q SDUCR/L07
Minimum pre-drill Ø D_{min}	20 mm
Pack of insert screws	269028 7
Insert size	7 mm
Centre offset L_3	11 mm
suitable indexable insert	DC.. 0702..
Overall length L	180 mm
Clamping height L_2	14 mm
Setting angle κ	93 degrees
Shank Ø D_s	16 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8