

**Garant**
**HSS boring bar AH.. SDUCL, for indexable inserts DC., left-hand**

**Order data**

Order number	260335
GTIN	4045197653062
Item class	29W

**Technical description**

suitable indexable insert	DC.. 0702..
ISO code toolholder	AH0810H SDUCR/L07
ISO code toolholder	AH1216M SDUCR/L07
ISO code toolholder	AH1012K SDUCR/L07
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{min}$	12.5 mm
Minimum pre-drill $\varnothing D_{min}$	15.5 mm
Minimum pre-drill $\varnothing D_{min}$	19.5 mm
Clamping height $L_2$	9 mm
Clamping height $L_2$	11 mm
Clamping height $L_2$	15 mm
Centre offset $L_3$	7 mm
Centre offset $L_3$	9 mm
Centre offset $L_3$	11 mm

Head length L <sub>1</sub>	22 mm
Head length L <sub>1</sub>	28 mm
Head length L <sub>1</sub>	36 mm
Overall length L	100 mm
Overall length L	125 mm
Overall length L	150 mm
Neck width L <sub>4</sub>	8 mm
Neck width L <sub>4</sub>	10 mm
Neck width L <sub>4</sub>	12 mm
Usable depth T	5 mm
Usable depth T	5 mm
Usable depth T	5 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Type of product	Boring bar

## Accessories

Boring bar HSS Shank Ø / insert size 0810/07 mm	260333 0810/07
Boring bar HSS Shank Ø / insert size 1012/07 mm	260333 1012/07
Boring bar HSS Shank Ø / insert size 1216/07 mm	260333 1216/07
Boring bar HSS Shank Ø / insert size 8/07 mm	260333 8/07
Set of insert screws Type 7	269028 7