

**Garant**

**HSS boring bar AH.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 25/11mm**


**Order data**

Order number	260332 25/11
GTIN	4045197652966
Item class	21T

**Technical description**

Minimum pre-drill Ø $D_{min}$	32 mm
ISO code toolholder	AH25R SDUCR/L11
Overhang $L_1$	125 mm
Centre offset $L_3$	16 mm
Pack of insert screws	269028 8
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Overall length L	200 mm
Clamping height $L_2$	23 mm
Setting angle $\kappa$	93 degrees
Shank Ø $D_s$	25 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15