

Garant

Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	260342 20/11
GTIN	4045197653093
Item class	21T

Technical description

suitable indexable insert	DC.. 11T3..
Centre offset L_3	13 mm
Insert size	11 mm
Pack of insert screws	269028 8
ISO code toolholder	A20R SDUCR/L11
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15