

Garant

Steel boring bar A.. SDUCR 93°, for indexable inserts DC., right-hand, Shank Ø / insert size: 40/11mm


Order data

Order number	260342 40/11
GTIN	4045197656056
Item class	21T

Technical description

Shim	269005 3
Pack of insert screws	269028 2
ISO code toolholder	A40T SDUCR/L11
Centre offset L_3	27 mm
Shim screw	269013 2
Minimum pre-drill $\varnothing D_{\min}$	49 mm
Insert size	11 mm
suitable indexable insert	DC.. 11T3..
Overall length L	300 mm
Clamping height L_2	39 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	40 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Shim Type 3	269005 3
Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15