

**Garant**

**Steel boring bar A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank  $\varnothing$  / insert size: 16/07mm**


**Order data**

|              |               |
|--------------|---------------|
| Order number | 260343 16/07  |
| GTIN         | 4045197653123 |
| Item class   | 21T           |

**Technical description**

|   |                               |
|---|-------------------------------|
| Centre offset $L_3$                     | 11 mm                         |
| Pack of insert screws                   | 269028 7                      |
| Minimum pre-drill $\varnothing D_{min}$ | 20 mm                         |
| suitable indexable insert               | DC.. 0702..                   |
| Insert size                             | 7 mm                          |
| ISO code toolholder                     | A16Q SDUCR/L07                |
| Overall length L                        | 180 mm                        |
| Clamping height $L_2$                   | 14 mm                         |
| Setting angle $\kappa$                  | 93 degrees                    |
| Shank $\varnothing D_s$                 | 16 mm                         |
| Standard                                | DIN 8024                      |
| Application type                        | left-hand                     |
| Boring depth up to                      | 3×D                           |
| Through-coolant                         | yes                           |
| Application                             | Internal longitudinal turning |
| Type of product                         | Boring Bar                    |

---

## Accessories

|  |            |
|--|------------|
| Set of insert screws Type 7  | 269028 7   |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8                             | 674248 TX8 |