

**Garant**

**Steel boring bar A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 25/11mm**


**Order data**

Order number	260343 25/11
GTIN	4045197653147
Item class	21T

**Technical description**

Centre offset $L_3$	17 mm
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Pack of insert screws	269028 8
Insert size	11 mm
ISO code toolholder	A25R SDUCR/L11
suitable indexable insert	DC.. 11T3..
Overall length L	200 mm
Clamping height $L_2$	24 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15