

Garant

Steel boring bar A.. SDUCL 93°, for indexable inserts DC.., left-hand, Shank Ø / insert size: 40/11 mm



Order data

Order number	260343 40/11
GTIN	4045197656025
Item class	21T

Technical description

Minimum pre-drill Ø D _{min}	49 mm
suitable indexable insert	DC.. 11T3..
Shim	269005 3
Insert size	11 mm
Shim screw	269013 2
Pack of insert screws	269028 2
ISO code toolholder	A40T SDUCR/L11
Centre offset L ₃	27 mm
Overall length L	300 mm
Clamping height L ₂	39 mm
Setting angle κ	93 degrees
Shank Ø D _s	40 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Shim Type 3	269005 3
Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15