

**Boring bar set, steel, with IC, right-hand, Type: SET07****Order data**

Order number	260346 SET07
GTIN	4045197656667
Item class	29W

Description**Supplied with:**

Plastic case

Technical description

suitable indexable insert	DC.. 0702..
ISO code toolholder	A1216M SDUCR/L07
ISO code toolholder	A0810H SDUCR/L07
ISO code toolholder	A1012K SDUCR/L07
Pack of insert screws	269028 7
Head length L ₁	22.5 mm
Head length L ₁	27.5 mm
Head length L ₁	40.5 mm
Clamping height L ₂	9 mm

Clamping height L ₂	11 mm
Clamping height L ₂	15 mm
Centre offset L ₃	6.5 mm
Centre offset L ₃	9 mm
Centre offset L ₃	11 mm
Minimum pre-drill Ø D _{min}	12 mm
Minimum pre-drill Ø D _{min}	15.5 mm
Minimum pre-drill Ø D _{min}	19 mm
Neck width L ₄	8 mm
Neck width L ₄	10 mm
Neck width L ₄	12 mm
Overall length L	100 mm
Overall length L	125 mm
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Type of product	Boring bar

Accessories

Boring bar steel Shank Ø / insert size 0810/07 mm	260342 0810/07
Boring bar steel Shank Ø / insert size 1012/07 mm	260342 1012/07
Boring bar steel Shank Ø / insert size 1216/07 mm	260342 1216/07
Boring bar steel Shank Ø / insert size 1012/07 mm	260343 1012/07
Boring bar steel Shank Ø / insert size 1216/07 mm	260343 1216/07
Set of insert screws Type 7	269028 7
	659957 500

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8