

Garant

**Clamping toolholder MTJNR 93°, for indexable inserts TN., right-hand,
Shank / insert size: 32/22mm**



Order data

Order number	251406 32/22
GTIN	4045197656919
Item class	21T

Technical description

Shank size	32 mm
Pin	259049 2
Head length L ₁	36 mm
Insert size	22 mm
Shim	259031 33
Functional width L ₄	40 mm
Clamping claw	259038 13
suitable indexable insert	TN.. 2204..
Screw set	259023 2
ISO code toolholder	MTJNR/L 3232P22
Overall length L	170 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of screws 10 pieces Type 2	259023 2
Shim Type 33	259031 33
Clamping claw Type 13	259038 13
Pin Type 2	259049 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 3 mm	674242 3