

Garant

Steel boring bar A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	260343 10/07
GTIN	4045197656001
Item class	21T

Technical description

suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	13.5 mm
Head length L_1	40 mm
Centre offset L_3	7 mm
ISO code toolholder	A10K SDUCR/L07
Overall length L	125 mm
Clamping height L_2	9 mm
Setting angle κ	93 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8