

Garant

Steel boring bar A.. SDUCL 93°, for indexable inserts DC., left-hand, Shank Ø / insert size: 12/07mm


Order data

Order number	260343 12/07
GTIN	4045197653116
Item class	21T

Technical description

Minimum pre-drill Ø D_{min}	16 mm
Insert size	7 mm
Centre offset L_3	9 mm
ISO code toolholder	A12L SDUCR/L07
suitable indexable insert	DC.. 0702..
Pack of insert screws	269028 7
Overall length L	140 mm
Clamping height L_2	11 mm
Setting angle κ	93 degrees
Shank Ø D_s	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8