

**Clamping toolholder SCLCR 95°, for indexable inserts SC., right-hand, Shank / insert size: 25/09mm****Order data**

Order number	260048 25/09
GTIN	4067263109631
Item class	22E

Description**Version:**

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Insert size	9 mm
ISO code toolholder	SCLCR/L 2525M09
Head length L ₁	19 mm
Pack of insert screws	269028 2
Overall length L	150 mm
Functional width L ₄	32 mm
suitable indexable insert	CC.. 09T3..
Standard	Works standard
Shank size	25 mm
Application type	right-hand
Through-coolant	yes

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver Type TX15	659950 TX15