



**for indexable inserts SD.. SVJC 93°, right-hand, Shank / insert size: 25/11mm**



## Order data

Order number	261300 25/11
GTIN	4067263109433
Item class	22E

## Description

### Version:

Targeted cooling on the cutting edge.

### Note:

Coolant transfer under the head via hose connection (G 1/8 inch – included in delivery).

## Technical description

Shank size	25 mm
ISO code toolholder	SVJCR/L 2525M11
suitable indexable insert	VC.. 1103..
Head length L <sub>1</sub>	26 mm
Functional width L <sub>4</sub>	32 mm
Insert size	11 mm
Standard	Works standard
Overall length L	150 mm
Pack of insert screws	269028 22
Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver Type TX15	659950 TX15
Torque screwdriver Type TX8	659950 TX8