



for indexable inserts SD.. SVJC 93°, right-hand, Shank / insert size: 25/11mm



Order data

Order number	261301 25/11
GTIN	4067263109457
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G 1/8 inch – included in delivery).

Technical description

Pack of insert screws	269028 22
Overall length L	150 mm
Functional width L ₄	32 mm
Shank size	25 mm
Standard	Works standard
ISO code toolholder	SVJCR/L 2525M11
Insert size	11 mm
suitable indexable insert	VC.. 1103..
Head length L ₁	26 mm
Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver Type TX15	659950 TX15
Torque screwdriver Type TX8	659950 TX8