

Garant
Clamping toolholder SRDCN 30°, for indexable inserts RC.X, neutral, Shank / insert size: 16/10mm

Order data

Order number	260611 16/10
GTIN	4045197653239
Item class	21T

Technical description

Functional width L ₄ neutral holders	13 mm
Pack of insert screws	269028 2
Overall length L neutral holders	100 mm
suitable indexable insert	RC.T 1003
Insert size	10 mm
Overhang L ₁ neutral holders	20.3 mm
Shank size	16 mm
Shim screw	269013 2
Shim	269005 11
ISO code toolholder	SRDCN 1616H10
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

Accessories

Shim Type 11	269005 11
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8