

Garant

Clamping toolholder SSSCL 45°, for indexable inserts SC., left-hand, Shank / insert size: 12/09mm



Order data

Order number	260707 12/09
GTIN	4045197655424
Item class	21T

Technical description

Head length L ₁	18 mm
suitable indexable insert	SC.. 09T3..
ISO code toolholder	SSSCR/L 1212F09
Functional width L ₄	16 mm
Pack of insert screws	269028 2
Shank size	12 mm
Insert size	9 mm
Overall length L	80 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15