

Garant

Clamping toolholder SSSCL 45°, for indexable inserts SC., left-hand, Shank / insert size: 20/09mm



Order data

Order number	260707 20/09
GTIN	4045197653338
Item class	21T

Technical description

Pack of insert screws	269028 2
Insert size	9 mm
Functional width L ₄	25 mm
suitable indexable insert	SC.. 09T3..
Shim	269005 12
Shank size	20 mm
ISO code toolholder	SSSCR/L 2020K09
Shim screw	269013 2
Head length L ₁	20 mm
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 12	269005 12
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15