

Garant
Clamping toolholder SSDCN 45°, for indexable inserts SC., neutral, Shank / insert size: 12/09mm

Order data

Order number	260711 12/09
GTIN	4045197655431
Item class	21T

Technical description

Functional width L ₄ neutral holders	6 mm
Overhang L ₁ neutral holders	6 mm
Insert size	9 mm
Shim screw	269013 2
Shank size	12 mm
suitable indexable insert	SC.. 09T3..
Overall length L neutral holders	80 mm
ISO code toolholder	SSDCN 1212F09
Pack of insert screws	269028 2
Shim	269005 12
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 12	269005 12
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15