

**Garant**
**Clamping toolholder SSDCN 45°, for indexable inserts SC., neutral, Shank / insert size: 16/09mm**

**Order data**

Order number	260711 16/09
GTIN	4045197655448
Item class	21T

**Technical description**

Shim screw	269013 2
Shank size	16 mm
Insert size	9 mm
Functional width L <sub>4</sub> neutral holders	8 mm
Overall length L neutral holders	100 mm
Pack of insert screws	269028 2
ISO code toolholder	SSDCN 1616H09
Overhang L <sub>1</sub> neutral holders	9 mm
Shim	269005 12
suitable indexable insert	SC.. 09T3..
Standard	DIN ISO 5610
Application type	neutral
Through-coolant	no
Setting angle κ	45 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 12	269005 12
Shim screw Type 2	269013 2
Set of insert screws Type 2	269028 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15