

**Garant**

**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,  
Shank / insert size: 25/16mm**



### Order data

Order number	250018 25/16
GTIN	4045197654311
Item class	21T

### Technical description

Insert size	16 mm
Functional width L <sub>4</sub>	32 mm
Shim	259031 35
Lever screw	259018 11
Shim pins pack	259044 6
Shim punches pack	259047 4
Head length L <sub>1</sub>	33 mm
Lever	259015 12
Shank size	25 mm
suitable indexable insert	CN.. 1606..
ISO code toolholder	PCLNR/L 2525M16
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4