

Garant

**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 32/16mm**



Order data

Order number	250018 32/16
GTIN	4045197649973
Item class	21T

Technical description

Shank size	32 mm
Functional width L ₄	40 mm
Lever	259015 12
Insert size	16 mm
Head length L ₁	40 mm
Lever screw	259018 11
Shim pins pack	259044 6
Shim	259031 35
Shim punches pack	259047 4
ISO code toolholder	PCLNR/L 3232P16
suitable indexable insert	CN.. 1606..
Overall length L	170 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4