

Garant
**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 32/19mm**

Order data

Order number	250018 32/19
GTIN	4045197649980
Item class	21T

Technical description

Shim punches pack	259047 5
Insert size	19 mm
suitable indexable insert	CN.. 1906..
Head length L ₁	40 mm
ISO code toolholder	PCLNR/L 3232P19
Shim	259031 36
Lever screw	259018 13
Shim pins pack	259044 7
Functional width L ₄	40 mm
Lever	259015 13
Shank size	32 mm
Overall length L	170 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 13	259015 13
Lever screw Type 13	259018 13
Shim Type 36	259031 36
Set of shim pins 10 pieces Type 7	259044 7