

**Garant**
**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,  
Shank / insert size: 16/09mm**

**Order data**

Order number	250018 16/09
GTIN	4045197649911
Item class	21T

**Technical description**

suitable indexable insert	CN.. 09T3..
Shim punches pack	259047 3
Lever screw	259018 6
Lever	259015 9
Shim	259031 27
Functional width L <sub>4</sub>	20 mm
Head length L <sub>1</sub>	25 mm
ISO code toolholder	PCLNR/L 1616H09
Shank size	16 mm
Insert size	9 mm
Shim pins pack	259044 5
Overall length L	100 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3