

**Garant**

**Clamping toolholder PCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 20/09mm**



## Order data

Order number	250019 20/09
GTIN	4045197649997
Item class	21T

## Technical description

Shank size	20 mm
Shim punches pack	259047 3
Lever	259015 9
Head length L <sub>1</sub>	28 mm
Shim	259031 27
Insert size	9 mm
Lever screw	259018 6
Shim pins pack	259044 5
ISO code toolholder	PCLNR/L 2020K09
suitable indexable insert	CN.. 09T3..
Functional width L <sub>4</sub>	25 mm
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3