

Garant
**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 20/09mm**

Order data

Order number	250018 20/09
GTIN	4045197649928
Item class	21T

Technical description

Shim pins pack	259044 5
ISO code toolholder	PCLNR/L 2020K09
Insert size	9 mm
suitable indexable insert	CN.. 09T3..
Lever screw	259018 6
Shim punches pack	259047 3
Shim	259031 27
Lever	259015 9
Head length L ₁	28 mm
Functional width L ₄	25 mm
Shank size	20 mm
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3